

## Solvent Degassing Systems Gastorr BG Series



Gastorr BG-32

Gastorr BG-34

A degassing system with settable vacuum levels and self-cleaning function.

### Features


- Complete self-cleaning function with independent chamber and vacuum pump
- Settable vacuum levels to handle specialty solvents
- New chamber design for thorough degassing of even low volumes
- CPU control achieves stable vacuum control
- Real time display of chamber vacuum level
- Independent chamber design prevents solvent contamination
- Error detection alerts user to faulty degassing operation
- RS-232C interface for computer control
- Choose from 2 channel or 4 channel configurations

Product name	Gastorr	
Part number	BG-32-02	BG-34-02
Channels	2	4
Internal volume	510 $\mu$ L	
Max flow rate	10 mL/min	
Degassing efficiency	Refer to below "Flow Rate and Dissolved Oxygen Level"	
Vacuum level	Adjustable with Up/Down keys (70~170 hPa)	
Vacuum range	2 hPa	
Thread size	1/4-28UNF	
Wetted materials	Teflon AF <sup>®</sup> , ETFE, PPS	
Communication	RS232C	
Dimensions	130 (H) x 70 (W) x 271 (D) mm (excluding protuberances)	
Weight	2.4 kg	
Power consumption	0.8 A, 80 VA	
Voltage range	AC100~240 V 50/60 Hz	
Order code	SGA-G2001	SGA-G2002

Note: The specifications and product design may change without prior notice.  
For custom specifications, contact FLOM.  
All trademarks are property of their respective owners.

### Flow Rate and Dissolved Oxygen Level

- Solvent: Distilled water 25  $^{\circ}$ C
- Vacuum level: 70 hPa
- Degassing unit: BG-34-02



\* The data is the result from experiments performed at our factory. Contact FLOM for details.